


PICOSECOND LASER

Spot Size 2-10mm Adjustable
Pulse Width 500ps
7 Joint Laser Arm



PRODUCT DISPLAY



HANDLE DISPLAY

7 Joint Light Guide Arm

Dirt-Proof Boot

Red Aiming Connection



Adjustable Spot Size


TREATMENT HEADS



1
1064nm&532nm

Black, blue, ink, brown, orange etc all colour tattoo removal.

Chloasma, dermis spot, age pigment, birthmark and nevus of ota etc pigmentation removal.



2
1320nm

Laser Carbon Peeling



3
755nm

Speckle Removal

TECHNICAL ADVANTAGE



2-10mm adjustable
spot size



Two lamps and *double rods*
laser system, stable output
energy, longer service life.




Korea Imported Aiming beam,
low maintenance and optical
loss, high stability and long
lifetime.





Light guide arm 360 treatment
without dead angle and ensure the
highest energy output minimum
energy loss during laser transmis-
sion.

Traditional Nd Yag Technology VS Picolaser Technology



Traditional Nd Yag Technology

The traditional picolaser pulse is longer and can only shattered the pigment to the size of a cobblestone. The absorption is slower, the recovery period is longer, and there may be anti-blackening, scars and blisters...



Picolaser Technology

Picolaser uses very short pulse output mode. pigment is "shattered" into finely granular via focused energy, are more likely to be absorbed by the body metabolism. Picolaser minimizes the side effects of thermal effects and can almost solve all kinds of pigment spots without a recovery period.



VS

BEFORE&AFTER



Before

After



Before

After



Before

After



Before

After



Before

After



Before

After

PARAMETER

Technical Parameters

Laser Type	TitanPico
Maximum Output Energy	1200Mj(1064nm) 600Mj(532nm)
Xenon Lamp	Single lamp or Double lamps
Laser Bar	Double rods
Treatment Heads	1064nm/532nm/1320nm/755nm Heads
Spot Size	2-10mm Adjustable
Pulse Frequency	1-10Hz
Voltage	110V/220V



COMPANY PROFILE



WAREHOUSE

Ample spare parts reserve.
Rich shell options.
Instant delivery time.



OEM/ODM

UNT has a strong research and development team, including electronics engineers (designer; AVR programming; circuit layout) construction engineer, UI designer engineer QC control engineer...etc. We provide OEM/ODM design and program update.



ABILITY

In UNT we have been at the forefront of laser diode technology since 2010, We are committed with the clinics and practices to deliver them a platform that gives them the ability to get there results that the customers demand.



Beijing UNT Technology CO.,Ltd

Address: No.M2-1, Xinggu Development Zone, Pinggu District, Beijing China. 101200

Website: <https://untlaser.en.alibaba.com/>

www.untlaser.com

Contact: 86-010-61960002